

## InTemp<sup>®</sup> CX402-VFCxxx

### Bluetooth Temperature with Glycol Bottle (VFC/CDC)

InTemp<sup>®</sup> CX402-VFCxxx (with glycol bottle) data loggers monitor temperatures in refrigerators and freezers for clinics participating in the CDC Vaccines for Children program as well as hospitals, clinics, and WHO sites. The loggers communicate wirelessly via Bluetooth Low Energy to mobile devices. Using the InTemp app, you can easily view data, check logger status, set alarms, and create and share secure PDF reports for streamlined reporting and regulatory compliance. All loggers feature a built-in LCD display to view current and daily min and max temperatures, advanced audible and visual alarm capabilities for notification of temperature excursions, an internal sensor for ambient temperature monitoring, and a 3-year NIST Certification of Calibration (probe only).

With the optional CX Gateway, you can get remote notifications of temperature excursions and automatically download data from loggers within range of the device. Learn more about the CX Gateway [here](#).

Models are available with a 2- or 4-meter external temperature probe attached to a glycol bottle used to insulate the probe and delay thermal response times.

#### Product Numbers:

CX402-VFC205  
CX402-VFC215  
CX402-VFC405  
CX402-VFC415


#### Key Advantages:

##### Features

- Complies with all CDC and Vaccine for Children (VFC) program requirements
- Integrates with mobile and cloud platforms for a 21 CFR Part 11 compliant solution
- Easy-to-read display with current and daily min/max temperatures
- Bluetooth transmission of data and alarm states
- Real-time alerts and automatic data downloads with optional CX Gateway device
- Logger setup and download of data in seconds – without a PC or cable
- +/- 0.5C accuracy for reliable temperature readings
- Battery-powered to guard against local power loss
- Several glycol bottle sizes with probe and cable-length options
- Includes 3-year ISO 17025 compliant calibration, [per CDC guidelines](#)



## InTemp CX402-VFCxxx Specifications

External Temperature Probe	
Range	-40° to 100°C (-40° to 212°F)
Accuracy	±1.0°C from -40° to -25°C (±1.8°F from -40° to -13°F) ±0.5°C from -25° to 80°C (±0.9°F from -13° to 176°F) ±1.0°C from 80° to 100°C (±1.8°F from 176° to 212°F)
Resolution	0.024°C at 25°C (0.04°F at 77°F)
NIST Calibration	Single point NIST calibration, probe only
Cable Length	2 or 4 meter (6.56 or 13.12 feet) flat ribbon cable
Probe Dimensions	Food-grade stainless steel probe with pointed tip, 53.34 mm (2.1 inches) long, 3.18 mm (0.125 inches) diameter
Temperature Sensor	
Range	-30° to 70°C (-22° to 158°F)
Accuracy	±1.0°C from -30° to -22°C (±1.8°F from -22° to -8°F) ±0.5°C from -22° to 50°C (±0.9°F from -8° to 122°F) ±1.0°C from 50° to 70°C (±1.8°F from 122° to 158°F)
Resolution	0.024°C at 25°C (0.04°F at 77°F)
Logger	
Radio Power	1 mW (0 dBm)
Transmission Range	Approximately 30.5 m (100 ft) line-of-sight
Wireless Data Standard	Bluetooth Low Energy (Bluetooth Smart)
Logger Operating Range	-30° to 70°C, 0 to 95% RH (non-condensing) (-22° to 158°F, 0 to 95% RH (non-condensing))
Logging Rate	1 second to 18 hours
Battery Type	Two AAA 1.5 V alkaline or lithium batteries, user replaceable
Battery Life	1 year, typical with logging interval of 1 minute. Faster logging intervals, remaining connected with the InTemp app, excessive report generation, numerous audible alarms, and paging all impact battery life.
Memory	128 KB (84,650 measurements, maximum)
Full Memory Download Time	Approximately 60 seconds; may take longer the farther the device is from the logger
LCD	LCD is visible from 0° to 50°C (32° to 122°F); the LCD may react slowly or go blank in temperatures outside this range
Dimensions	9.4 x 4.5 x 2.59 cm (3.7 x 1.77 x 1.02 inches)
Weight	90.2 g (3.18 oz)
Environmental Rating	IP54
Compliance Marks	

## Contact Us

Sales (8am to 5pm ET, Monday through Friday)

- ▶ Email [sales@onsetcomp.com](mailto:sales@onsetcomp.com)
- ▶ Call 1-508-759-9500
- ▶ In U.S. toll free 1-800-564-4377
- ▶ Fax 1-508-759-9100

Technical Support (8am to 6pm ET, Monday through Friday)

- ▶ Contact Product Support [www.onsetcomp.com/support/contact](http://www.onsetcomp.com/support/contact)
- ▶ Call 1-508-759-9500
- ▶ In U.S. toll free 1-877-564-4377

Onset Computer Corporation  
470 MacArthur Boulevard  
Bourne, MA 02532